



Representative

Catalog Number: 54208NTUB
Product ID: 7TAH007990R0642
UPC Number: 78620999626
Status: Active

Copper Two-Hole Lug, 90 Degree Bend Standard Barrel, Narrow Tongue, Peep Hole, Max 35kV, Wire Size #1 AWG, 1/4 Inch Bolt Size, 5/8 Inch Hole Spacing, Tin Plated, Die Code 37, Die Color Code Green

North American Specifications (UNSPSC)

UNSPSC	39121405 Cable or wire lug
IGCC	4532 Cable or wire lug
Brand Name	Color-Keyed
Type	Standard Barrel 90 Degree Bend
Cable Size	#1 AWG
Stud Size	1/4 Inch
Number Of Holes	2
Voltage Rating	Max 35kV
Insulation	None
Material	Copper
Color	Green

European Specifications (ETIM)

ETIM	EC001051 Tube cable lug for copper conductors
Connecting angle	90°
Slender flange model	Y
Insulated	N
With sight-hole	Y
Material	Copper
Surface protection	Tinned
Number of fixing holes	2

Packaging

Inner Quantity	20
Inner Dimensions (inches)	3.25x2.75x2.25
Outer Quantity	200
Outer Dimensions (inches)	12.18x6x3.31
Weight Uom	6.25 lbs. per 100

Documents / Support Tools

Technical Drawing / Data Sheet	WSD-002068
Technical Drawing / Data Sheet Canada	Available on Website