



Actual

**Catalog Number:** 5713  
**Product ID:** 7TAD012560R0003  
**UPC Number:** 78621005713  
**EAN Number:** 05414363144731  
**Status:** A

1-1/4 Inch Neoprene Liquidtight Knockout Plug

- Made of flame retardant neoprene, these new knockout plugs meet U.L. 514 flammability test.
- Provide a raintight, dust and oil-tight reusable seal for electrical knockouts.
- NEMA 3R, 4, 6 and 13 boxes can be saved or re-used whenever a knockout is no longer used.
- No tools needed to install; just push into hole and they snap in

### North American Specifications (UNSPSC)

UNSPSC	39121420 Liquid tight connectors
IGCC	4585 Liquid tight connectors
Type	Knockout Plugs
Standard	UL E13938
Size	1-1/4 Inch
Material	Neoprene

### European Specifications (ETIM)

ETIM	EC000032 Plug for cable screw gland
Thread type	NPT
Nominal thread size inch/gas pipe thread	1 1/4 inch
Material	Plastic
Material quality	Other
Colour	Black

### Packaging

Inner Quantity	25
Inner Dimensions (inches)	6x5x4
Outer Quantity	125
Outer Dimensions (inches)	5.4x26.9x7.1
Weight Uom	5 lbs. per 100

### Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
Catalog Page	Available on Website

### Header

3D Model	Available on Website
----------	----------------------