



Actual



Actual

**Catalog Number:** 6302SST  
**Product ID:** 7TAD012080R0000  
**UPC Number:** 78620991372  
**EAN Number:** 05415022435474  
**Status:** A

1/2 Inch Stainless Steel Type A Liquidtight Straight Connector With Santoprene Sealing Gasket and Stainless Steel Retaining Ring

**North American Specifications (UNSPSC)**

UNSPSC	39121420 Liquid tight connectors
IGCC	4585 Liquid tight connectors
Type	Connectors-Straight
Standard	UL E23018
Size	1/2 Inch
Material	Stainless Steel

**European Specifications (ETIM)**

ETIM	EC001178 Screw connection for protective plastic hose
Nominal size in inch	1/2 inch
Model	Straight
Revolving thread	N
Construction type	External thread
Type of connection	Thread
Thread connection size	Other
Thread length	15.24mm
One-piece	N
Material screw gland	Metal

**Packaging**

Inner Quantity	20
Inner Dimensions (inches)	6.25x4.75x4.25
Outer Quantity	100
Outer Dimensions (inches)	21.62x5.12x6.62
Weight Uom	37.5 lbs. per 100

**Documents / Support Tools**

Technical Drawing / Data Sheet US	Available on Website
-----------------------------------	----------------------

**Header**

3D Model	Available on Website
----------	----------------------