



Actual



Representative

Catalog Number: 6324
Product ID: 7TAD012490R0005
UPC Number: 78621006324
EAN Number: 05414363145394
Status: A

1 Inch 90 Degree Non-metallic Type A Liquidtight Connector With Captive Sealing O-ring and Tapered Hub Thread

- Serrated design provides high mechanical pull-out strength.
- Unique component parts (body/gland) design ensures positive seal between conduit and connector.
- Tapered thread hub and furnished neoprene sealing O-ring provide a liquidtight, dust-tight seal to a box or enclosure.
- Smooth insulated body throughout for maximum dielectric strength.
- Captive O-ring and reduced number of parts save installation time.
- Chemical resistant, ideal for corrosive environments
- Ideal for automotive and automotive OEM applications, electric signs and outdoor lighting over 1000V (Article 600.31(A)), and pool and spa wiring. (Article 680)

North American Specifications (UNSPSC)

UNSPSC	39121420 Liquid tight connectors
IGCC	4585 Liquid tight connectors
Type	Connectors-90 Degree
Application	To provide a liquidtight; dust tight connection between flexible, non-metallic conduit and a box or an enclosure.
Standard	UL E23018
Size	1 Inch
Material	Thermoplastic

European Specifications (ETIM)

ETIM	EC001178 Screw connection for protective plastic hose
Nominal size in inch	1 inch
Model	90°-elbow
Revolving thread	N
Construction type	External thread
Type of connection	Thread
Thread connection size	Other
Thread length	19.56mm
One-piece	N
Material screw gland	Other

Packaging

Inner Quantity	5
Outer Quantity	25
Outer Dimensions (inches)	12.8x10.5x5.13
Weight Uom	34.38 lbs. per 100

Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
Catalog Page	Available on Website
Instruction Sheet	TA01782-TB2

Header

3D Model

Available on Website