



Representative

Catalog Number: 7355
Product ID: 7TAD012330R0020
UPC Number: 78621007355
EAN Number: 05414363100225
Status: A

1 Inch 90 Degree Steel Insulated Liquidtight Connector With PG Thread and Chromate Finish, Thread Size 29

- Quick and easy to install by hand, no special tool needed.
- Provides a positive seal against oil, liquids, moisture and dust

North American Specifications (UNSPSC)

UNSPSC	39121420 Liquid tight connectors
IGCC	4585 Liquid tight connectors
Type	Liquidtight Flexible Metal Conduit Fittings
Special Features	CSA Certified Dusttight and Watertight. UL Listed Liquidtight.
Application	Nylon Insulated 90D Angle Fittings
Standard	CSA, UL E23018
Size	1 Inch
Material	Nylon Insulated

European Specifications (ETIM)

ETIM	EC001180 Screw connection for protective metallic hose
Nominal size in inch	1 inch
Model	90°-elbow
Revolving thread	N
Construction type	External thread
Connection type screw connection to housing	Thread
Thread type	Other
Thread connection size	PG29
One-piece	N
Material housing	Steel
Thread length	21mm
Approved in combination with protective conduit CSA	Y
Approved in combination with protective conduit UL	Y

Packaging

Inner Quantity	5
Inner Dimensions (inches)	6x4.5x3
Outer Quantity	25
Outer Dimensions (inches)	24.2x6.2x3.5
Weight Uom	50 lbs. per 100

Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
Instruction Sheet	TA00210-TB2
Support/Tools	Available on Website
Marketing Brochure	Available on Website
Catalog US	Available on Website

Header

3D Model	Available on Website
----------	----------------------

