



Actual



Representative

Catalog Number: 8220
Product ID: 7TAD013160R0024
UPC Number: 78621008220
EAN Number: 05414363183129
Status: A

3/4 Inch Coupling, Malleable Iron for Use with Threadless Rigid/IMC Conduit

- Tightened with a wrench they make a U.L. Listed and CSA Certified concrete-tight connection.
- To Connect Threaded Metal Conduit to a Threadless Opening in a Box or Enclosure

North American Specifications (UNSPSC)

UNSPSC	39131707 Electrical conduit coupling
IGCC	5548 Electrical conduit coupling
Type	Compression Couplings & Connectors
Special Features	Eliminate Conduit Threading.
Application	To Couple and Effectively Bond Threaded Ends of Rigid Metal Conduit/Intermediate Conduit Where Neither Length of Conduit Can Be Roated
Standard	UL E23018, CSA
Trade Size	3/4 in
Material	Malleable Iron

European Specifications (ETIM)

ETIM	EC000939 Coupler for installation tubes
Material	Metal
Material quality	Other
Model	Thread
Two piece	N
With inspection opening and cover	N

Packaging

Inner Quantity	25
Inner Dimensions (inches)	4x5x8
Outer Quantity	50
Outer Dimensions (inches)	9.6x7.2x10.3
Weight Uom	30.5 lbs. per 100

Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
Catalog Page	Available on Website

Header

3D Model	Available on Website
----------	----------------------