



Representative

**Catalog Number:** 8221  
**Product ID:** 7TAD013150R0000  
**UPC Number:** 78621008221  
**EAN Number:** 05414363146452  
**Status:** A

3/4 Inch Threadless Connector, Malleable Iron for Use with Rigid/IMC Conduit

#### North American Specifications (UNSPSC)

UNSPSC	39121311 Electrical fittings
IGCC	4441 Electrical fittings
Type	Threadless Connector
Application	To Connect and Effectively Bond Threadless Rigid Metal Conduit/Intermediate Metal Conduit to a Box or Enclosure, or to Couple Ends of Threadless Conduit
Standard	UL E23018, CSA
Size	3/4 Inch
Material	Malleable Iron

#### European Specifications (ETIM)

ETIM	EC001492 Coupler for cable protection tube
Material	Metal
Material quality	Other
Surface protection	Untreated
Colour	Natural colour
Outer diameter	44.45mm

#### Packaging

Inner Quantity	25
Inner Dimensions (inches)	4x5x8
Outer Quantity	50
Outer Dimensions (inches)	8.8x5.8x8.8
Weight Uom	25.88 lbs. per 100

#### Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
-----------------------------------	----------------------

#### Header

3D Model	Available on Website
----------	----------------------