


## Couplings and Accessories

Split steel ring with diagonal serrations grips conduit and bites in for positive ground!

### Threadless Connectors — Nylon Insulated

- Makes a permanent connection
- Eliminates need for cutting a thread on conduit
- Insulation helps ensure continuity of service by protecting the conductor at the critical point — the connector bushing
- Malleable iron construction
- Look for the unique T&B blue color, ensuring the highest quality fitting



CAT. NO.		CONDUIT SIZE	DIMENSIONS (IN.)		
NYLON INSUL.	NON-INSUL.		A	B	C
8123	8121	1/2"	1 1/32	1 1/16	1/2
8223	8221	3/4"	1 1/32	1 3/4	1/2
8323	8321	1"	1 29/32	2	9/16
8423	8421	1 1/4"	2 3/8	2 7/16	1 1/16
8523	8521	1 1/2"	2 11/16	2 5/8	3/4
8623	8621	2"	3 1/4	2 13/16	27/32
8723-TB	8721	2 1/2"	4 1/8	3 13/16	1 1/8
8823	8821	3"	4 7/8	4	1 1/32
8853	8851	3 1/2"	5 1/2	4 7/8	1 1/8
8973	8971	4"	6 1/32	4 7/8	1 1/8


Available with DURA-PLATE® Finish. UL File No. E-23018 CSA File No. 2884

Just tighten with a wrench to make a UL Listed and CSA Certified concrete-tight connection!



### Threadless Couplings

- Eliminates need for conduit threading
- Malleable iron construction




CAT. NO.	SIZE	DIMENSIONS (IN.)	
		A	B
8120	1/2"	1 9/32	2
8220	3/4"	1 19/32	2 5/16
8320	1"	1 7/8	2 11/16
8420	1 1/4"	2 5/8	2 13/16
8520	1 1/2"	2 5/8	3 5/8
8620	2"	3 3/4	3 13/16
8720	2 1/2"	3 15/16	5 3/8
8820	3"	4 11/16	5 1/2
8850	3 1/2"	5 3/16	5 1/2
8970	4"	5 11/16	5 1/2

Available with DURA-PLATE® Finish. UL File No. E-23018 CSA File No. 2884

Ideal for entering enclosure or conduit body at right angles!

### Threadless Short Elbows — Nylon Insulated

- Eliminates need to thread conduit
- As with straight couplings, makes a concrete-tight connection
- Malleable iron construction



CAT. NO.	SIZE	DIMENSIONS (IN.)		
		A	B	C
8130	1/2"	1 11/32	1 1/2	1/2
8131	3/4"	1 5/8	1 3/4	9/16
8132	1"	1 7/8	1 15/16	1 1/16

Available with DURA-PLATE® Finish. UL File No. E-23018 CSA File No. 2884