



Actual

Catalog Number: AC85X75
Product ID: 7TAA017410R0003
UPC Number: 78621083947
Status: A

Adhesive Insulating Cover 8.5 x 7.5 Inch Pad for H-Taps and C-Taps, 600 Volts, 80 Degrees Celsius, Vinyl Backing with Rubber Adhesive, Black

- Seals against moisture.
- No installing tools required.
- Seals connections against Moisture.

North American Specifications (UNSPSC)

UNSPSC	39121721 Electrical insulators
IGCC	5069 Electrical insulators
Type	Splice Insulators and Insulating Covers
Special Features	Seals against moisture.
Application	Seals connections against Moisture.
Standard	UL E9809
Voltage Rating	600 V
Material	6 mil electrical vinyl backing, butyl rubber mastic adhesive thickness approx. 1/8 inch, Polyethylene release sheet

European Specifications (ETIM)

ETIM	EC000128 Adhesive tape
Width	215.9mm
Material	Other
Colour	Black
Transparent	N
Reflective (fluorescent)	N
Length	0.1778m
Double-sided	N
UV resistant	N
Insulating	Y
Self-extinguishing	N
Temperature resistance	-10-+48°C
Thickness	3.175mm
Self sticking/amalgamating	Y
Suitable for high voltage	N
Vulcanizing	N

Packaging

Inner Quantity	5
Inner Dimensions (inches)	5.75x5.875x7.625
Outer Quantity	50
Outer Dimensions (inches)	18.5x13.25x13.5
Weight Uom	44 lbs. per 100

Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
Catalog Page	Available on Website
Instruction Sheet	TA04162-TB2
Safety Data Sheet (SDS) Global	SDS-00046-TB2

