



Other

Catalog Number: AL28/M25/A/BL
Product ID: 7TCA296000R0797
EAN Number: 05020963000713
Status: Active

Straight Conduit Fitting, Fixed External Male Thread, Nominal Conduit Size 28mm, M25 Thread, Polyamide (Nylon) 66, Black

North American Specifications (UNSPSC)

UNSPSC	39121311 Electrical fittings
IGCC	4441 Electrical fittings
Brand Name	Adaptaflex
Type	Conduit Fitting with Metric Threads
Application	For Insertion into Threaded Entries or Knockout to Connect Conduit
Size	NC 28mm
Material	Polyamide/Nylon 6.6
Color	Black
Connection	Straight
Cable Entry	M25 Thread

European Specifications (ETIM)

ETIM	EC001178 Screw connection for protective plastic hose
Nominal diameter	28mm
Nominal size in inch	3/4 inch
Degree of protection (IP)	IP66
Model	Straight
Revolving thread	N
Construction type	External thread
Type of connection	Snap connection
Thread connection size	M25 x 1.5
Thread length	16.2mm
One-piece	Y
Material screw gland	Polyamide
Total height	35.5mm
Total length	53mm
Colour	Black
Approved in combination with protective conduit DIN EN 61386-23	Y
Approved in combination with protective conduit UR	Y

Packaging

Inner Quantity	10
Inner Dimensions (inches)	2x6x6
Outer Quantity	150
Outer Dimensions (inches)	6x14x14
Weight Uom	3.75 lbs. per 100

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
 www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com