



Representative

**Catalog Number:** AL28/PG21/SA/BL  
**Product ID:** 7TCA296000R0873  
**EAN Number:** 05020963019494  
**Status:** Active

Straight Conduit Fitting, Swivel External Male Thread, Nominal Conduit Size 28mm, PG21 Thread, Polyamide (Nylon) 66, Nickel Plated Brass Thread, Black

### North American Specifications (UNSPSC)

UNSPSC	39121311 Electrical fittings
IGCC	4441 Electrical fittings
Brand Name	Adaptaflex
Type	Conduit Fitting with PG Threads
Application	For Insertion into Threaded Entries or Knockout to Connect Conduit
Size	NC 28mm
Material	Polyamide/Nylon 6.6
Color	Black
Connection	Straight
Cable Entry	PG21 Thread

### European Specifications (ETIM)

ETIM	EC001176 Screw connection for corrugated plastic hose
Nominal diameter	28mm
Degree of protection (IP)	IP66
Model	Straight
Revolving thread	Y
Construction type	External thread
Type of connection	Snap connection
Thread type	Other
Thread connection size	PG21
Thread length	11.5mm
Total length	34mm
Total height	60.2mm
Material	Polyamide
Colour	Black
Approved in combination with protective conduit UR	Y
Approved in combination with protective conduit DIN EN 61386-23	Y

### Packaging

Inner Quantity	10
Inner Dimensions (inches)	1.7x2.1x2
Outer Quantity	10
Outer Dimensions (inches)	1x2.1x2
Weight Uom	1.1 lbs. Each

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
 860 Ridge Lake Blvd.  
 Memphis, TN 38120  
 www.tnb.com

T&B Technical Support  
 MS 3B-50  
 860 Ridge Lake Blvd.  
 Memphis, TN 38120

Hours: 7AM - 6PM CDT  
 Monday-Friday  
 Phone: (888) 862-3289  
 Fax: (901) 252-1321  
 Email:techsupport@tnb.com