



Representative

**Catalog Number:** AL34/PG29/A/BL  
**Product ID:** 7TCA296000R1002  
**EAN Number:** 05020963006531  
**Status:** Active

Straight Conduit Fitting, Fixed External Male Thread, Nominal Conduit Size 34mm, PG29 Thread, Polyamide (Nylon) 66, Black

### North American Specifications (UNSPSC)

UNSPSC	39121311 Electrical fittings
IGCC	4441 Electrical fittings
Brand Name	Adaptaflex
Type	Conduit Fitting with PG Threads
Application	For Insertion into Threaded Entries or Knockout to Connect Conduit
Size	NC 34mm
Material	Polyamide/Nylon 6.6
Color	Black
Connection	Straight
Cable Entry	PG29 Thread

### European Specifications (ETIM)

ETIM	EC001176 Screw connection for corrugated plastic hose
Nominal diameter	34mm
Degree of protection (IP)	IP66
Model	Straight
Revolving thread	N
Construction type	External thread
Type of connection	Snap connection
Thread type	Other
Thread connection size	PG29
Thread length	12.2mm
Total length	41.5mm
Total height	50mm
Material	Polyamide
Colour	Black
Approved in combination with protective conduit UR	Y
Approved in combination with protective conduit DIN EN 61386-23	Y

### Packaging

Inner Quantity	10
Inner Dimensions (inches)	1.4x2x1.3
Outer Quantity	100
Outer Dimensions (inches)	1.4x2x1.3
Weight Uom	0.15 lbs. Each

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
 860 Ridge Lake Blvd.  
 Memphis, TN 38120  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
 MS 3B-50  
 860 Ridge Lake Blvd.  
 Memphis, TN 38120

Hours: 7AM - 6PM CDT  
 Monday-Friday  
 Phone: (888) 862-3289  
 Fax: (901) 252-1321  
 Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)