



Representative

**Catalog Number:** AL42/125/45/BLYI  
**Product ID:** 7TCA296000R1055  
**EAN Number:** 05020963782596  
**Status:** Active

45 Degree Conduit Fitting with Locknut and Sealing Washer, Fixed External Male Thread, Nominal Conduit Size 42mm, 1-1/4 Inch NPT Thread, Polyamide (Nylon) 66, Black

### North American Specifications (UNSPSC)

UNSPSC	39121311 Electrical fittings
IGCC	4441 Electrical fittings
Brand Name	Adaptaflex
Type	Conduit Fitting with NPT Threads
Application	For Insertion into Threaded Entries or Knockout to Connect Conduit
Size	NC 42mm
Material	Polyamide/Nylon 6.6
Color	Black
Connection	45 Degree
Cable Entry	1-1/4 Inch NPT Thread

### European Specifications (ETIM)

ETIM	EC001176 Screw connection for corrugated plastic hose
Nominal diameter	42mm
Degree of protection (IP)	IP66
Model	45°-elbow
Revolving thread	N
Construction type	External thread
Type of connection	Snap connection
Thread type	NPT
Thread connection size	Other
Thread length	16mm
Material	Polyamide
Material sealing	TPE
Colour	Black
Approved in combination with protective conduit UR	Y
Approved in combination with protective conduit DIN EN 61386-23	Y

### Packaging

Outer Quantity	2
Outer Dimensions (inches)	1x1x1
Weight Uom	0.14 lbs. Each

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
 860 Ridge Lake Blvd.  
 Memphis, TN 38120  
 www.tnb.com

T&B Technical Support  
 MS 3B-50  
 860 Ridge Lake Blvd.  
 Memphis, TN 38120

Hours: 7AM - 6PM CDT  
 Monday-Friday  
 Phone: (888) 862-3289  
 Fax: (901) 252-1321  
 Email: techsupport@tnb.com