



Representative

Catalog Number: AL54/PG48/A/BL
Product ID: 7TCA296000R1278
EAN Number: 05020963007248
Status: Active

Straight Conduit Fitting, Fixed External Male Thread, Nominal Conduit Size 54mm, PG48 Thread, Polyamide (Nylon) 66, Black

North American Specifications (UNSPSC)

UNSPSC	39121311 Electrical fittings
IGCC	4441 Electrical fittings
Brand Name	Adaptaflex
Type	Conduit Fitting with PG Threads
Application	For Insertion into Threaded Entries or Knockout to Connect Conduit
Size	NC 54mm
Material	Polyamide/Nylon 6.6
Color	Black
Connection	Straight
Cable Entry	PG48 Thread

European Specifications (ETIM)

ETIM	EC001176 Screw connection for corrugated plastic hose
Nominal diameter	54mm
Degree of protection (IP)	IP66
Model	Straight
Revolving thread	N
Construction type	External thread
Type of connection	Snap connection
Thread type	Other
Thread connection size	PG48
Thread length	12.1mm
Total length	67.2mm
Total height	64.9mm
Material	Polyamide
Colour	Black
Approved in combination with protective conduit UR	Y
Approved in combination with protective conduit DIN EN 61386-23	Y

Packaging

Inner Quantity	2
Inner Dimensions (inches)	2.8x2.5x2.5
Outer Quantity	40
Outer Dimensions (inches)	2.8x2.5x2.5
Weight Uom	0.16 lbs. Each

For further technical assistance, please contact us...

Thomas & Betts - USA
 860 Ridge Lake Blvd.
 Memphis, TN 38120
www.tnb.com

T&B Technical Support
 MS 3B-50
 860 Ridge Lake Blvd.
 Memphis, TN 38120

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com