



Family

**Catalog Number:** BLNO-M253  
**Product ID:** 7TAA292740R0010  
**UPC Number:** 78620999836  
**EAN Number:** 07630030206672  
**Status:** Active

LNO Divisible Connector Straight, One-Piece, Metric Thread - Thread Size M25x1.5, Fits to Conduit Size NW/Metric 23/25, Color Black

### North American Specifications (UNSPSC)

UNSPSC	39121311 Electrical fittings
IGCC	4441 Electrical fittings
Brand Name	PMA
Type	Connectors-Straight
Application	For Cable Protection Systems In a Wide Range of Applications
Size	NW23
Material	Polyamide 6
Insulation Class	IP54
Color	Black
Connection	M25
Temperature Rating	-40 Degrees C to 105 Degrees C; Short Term to 160 Degrees C

### European Specifications (ETIM)

ETIM	EC001176 Screw connection for corrugated plastic hose
Nominal diameter	25mm
Degree of protection (IP)	IP54
Model	Straight
Revolving thread	N
Construction type	Internal thread
Type of connection	Snap connection
Thread type	Metric
Thread connection size	M25 x 1.5
Thread material	Polyamide
Thread length	14mm
Total length	52.5mm
Total height	36.5mm
Material	Polyamide
Material sealing	No sealing
Colour	Black
Approved in combination with protective conduit CSA	N
Approved in combination with protective conduit UR	N
Approved in combination with protective conduit DIN EN 61386-23	N
Approved in combination with protective conduit Lloyd's Register	N
Operating temperature	-40 - +105°C

### Packaging

Inner Quantity	30
Outer Quantity	180
Outer Dimensions (inches)	15.748x11.811x8.661
Weight Uom	0.1 lbs. Each

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
860 Ridge Lake Blvd.  
Memphis, TN 38120  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
MS 3B-50  
860 Ridge Lake Blvd.  
Memphis, TN 38120

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)