



Family

Catalog Number: BLNO-M409
Product ID: 7TAA292740R0015
UPC Number: 78620999833
EAN Number: 07630030206627
Status: Active

LNO Divisible Connector Straight, One-Piece, Metric Thread - Thread Size M40x1.5, Fits to Conduit Size NW/Metric 29/32, Color Black

North American Specifications (UNSPSC)

UNSPSC	39121311 Electrical fittings
IGCC	4441 Electrical fittings
Brand Name	PMA
Type	Connectors-Straight
Application	For Cable Protection Systems In a Wide Range of Applications
Size	NW29
Material	Polyamide 6
Insulation Class	IP54
Color	Black
Connection	M40
Temperature Rating	-40 Degrees C to 105 Degrees C; Short Term to 160 Degrees C

European Specifications (ETIM)

ETIM	EC001176 Screw connection for corrugated plastic hose
Nominal diameter	32mm
Degree of protection (IP)	IP54
Model	Straight
Revolving thread	N
Construction type	Internal thread
Type of connection	Snap connection
Thread type	Metric
Thread connection size	M40 x 1.5
Thread material	Polyamide
Thread length	21mm
Total length	65mm
Total height	43mm
Material	Polyamide
Material sealing	No sealing
Colour	Black
Approved in combination with protective conduit CSA	N
Approved in combination with protective conduit UR	N
Approved in combination with protective conduit DIN EN 61386-23	N
Approved in combination with protective conduit Lloyd's Register	N
Operating temperature	-40 - +105°C

Packaging

Inner Quantity	20
Outer Quantity	100
Outer Dimensions (inches)	15.748x11.811x8.661
Weight Uom	0.1 lbs. Each

For further technical assistance, please contact us...

Thomas & Betts - USA
860 Ridge Lake Blvd.
Memphis, TN 38120
www.tnb.com

T&B Technical Support
MS 3B-50
860 Ridge Lake Blvd.
Memphis, TN 38120

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com