



Flexible Conduits & Fittings

T&B Catalog Number:

BVND-M12MGT

UPC Number:

78620995100

Status:

Active

Description:

PMAFIX straight black connector with universal safety clip. Material - polyamide 6, thread type - metric, thread size M12 x 1.5, conduit size NW - 07.

Application

For cable protection systems in a wide range of applications

Characteristics

Very high impact resistance
 Vibration proof connection to PMAFLEX conduits
 High conduit pull-out strength
 Very good chemical properties
 Free from halogens and cadmium
 Fits both conduit profiles - Fine (T) and coarse (G)
 Easy installation, simply push the conduit in
 Can be easily re-opened with a screwdriver

General

Material Polyamide 6
 Color Black
 Thread Type Metric
 Compatible With PMAFLEX, PMA Smart Line

Dimension Information

Fits to Conduit Size (NW) 07
 Fits to Conduit Size (metric) 10
 Fits to Conduit Size (inches) 1/4
 Thread Size (Metric) M12 x 1.5

Technical Information

Temperature Range-Continuous (Celsius) -40 degree C to +105 degree C
 Temperature-Short-Term (Celsius) +160 degree C
 Technical Data Sheet Available on Website
 Chemical Resistance Chart Available on Website

Specifications

3dmodel Available on Website

IP Ratings

IP Rating IP66 stat. / IP54 dyn.

Packaging

T&B Inner Pack 100
 Package in Units 1500
 T&B Sold in UOM Each
 T&B Weight Per UOM 0.01 lbs. Each

Application Support

PMA Reference Guide Available on Website
 Product Overview-PMAFIX Connectors Available on Website
 Available on Website

PMAFIX Connectors-Safety and Sealing
Systems

Certifications

RoHS Compliance	Yes
-----------------	-----

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com