

Device Boxes and Covers

Aluminum Single- and Double-Gang Covers



CWPDR

CWPDR-FS



CFSDR



CWP-G



CFSH-G



CWPV-G



CFSR-G



CFSR Series



CFST



CFSTF



CFSB

Single-Gang Covers — Raintight*

CAT. NO.	DESCRIPTION	UNIT QTY.	STD. PKG.	WT. LBS. PER 100
For Duplex Receptacles, Horizontal				
CWPDR*	Duplex Receptacle Cover with (2) Spring Doors, Device Mount	1	25	40
CWPDR-FS*	Box Mount	1	25	40

For Duplex Receptacles, Vertical				
CFSDR*	Box Mount	1	25	38

For GFCI Receptacles, Horizontal				
CFSH-G*	Box Mount	1	25	40

For GFCI Receptacles, Vertical				
CWPV-G*	GFCI Receptacle Cover, 2 ¹ / ₃₂ " x 1 ¹ / ₃₂ " Rectangular Opening Device Mount	1	25	40
CFSR-G*	Box Mount	1	25	40

*Raintight when used with appropriate Thomas & Betts boxes and gaskets. Suitable for use in wet locations with cover closed — NEMA 3R.

CAT. NO.	NOMINAL SIZE	MAX. DEVICE FACE DIA.	UNIT QTY.	STD. PKG.	WT. LBS. PER 100
For Single Receptacles, Vertical (Box Mount Only)					
CFSR-L*	1 ¹ / ₁₆ "	1.600"	1	25	40
CFSR-S*	1 ³ / ₈ "	1.395"	1	25	40
CFSR-X*	1 ²⁷ / ₃₂ "	1.865"	1	25	40
CFSR-XL*	2 ¹ / ₈ "	2.145"	1	25	40
CFSR-Y*	1 ³ / ₄ "	1.750"	1	25	40

*Raintight when used with appropriate Thomas & Betts boxes and gaskets. Suitable for use in wet locations with cover closed — NEMA 3R.

CAT. NO.	DESCRIPTION	UNIT QTY.	STD. PKG.	WT. LBS. PER 100
Switch Cover				
CFST*	Plunger Style, Switch Cover, Box Mount NEMA 3R	1	25	40
Switch Cover				
CFSTF*	Front Lever, Switch Cover, Box Mount NEMA 4	1	25	40
Blank Cover				
CFSB*	Blank Cover, Box Mount, NEMA 3R	1	25	14

*Raintight when used with appropriate Thomas & Betts boxes and gaskets. Suitable for use in wet locations with cover closed — NEMA 3R.