



Actual

Catalog Number: C112-90-AM2
Product ID: 7TCA298010R0242
EAN Number: 05020963023262
Status: Active

Hinged Connector Interface Fitting, 90 Degree Elbow with 360 Degree Swivel, 2-Way AMP Junior or Mini Timer Connector to Conduit, Conduit Size NC12/NW10, Operating Temperature -40 to 120 Degrees Celsius, RoHS Compliant, IP40 Rating, Very High UV Protection, Polyamide (Nylon), Black

North American Specifications (UNSPSC)

UNSPSC	39121421 Electrical connector assembly
IGCC	4586 Electrical connector assembly
Brand Name	Harnessflex
Type	Hinged AMP Junior or Mini Timer Connector to Conduit
Special Features	High Pull-Off Strength
Application	Provide Connection Between Connector Interface and Conduit
Standard	RoHS Compliant
Size	Conduit Size NC12/NW10
Connection	90 Degree Elbow with 360 Degree Swivel, 2-Way Connection
Material	Polyamide/Nylon
Color	Black
Insulation	IP40
Temperature Rating	-40 to 120 Degrees C
Environmental Conditions	Very High UV Protection

Packaging

Outer Quantity	500
Outer Dimensions (inches)	14x14x14
Weight Uom	1.11 lbs. per 100

Header

3D Model	Available on Website
----------	----------------------

For further technical assistance, please contact us...

Thomas & Betts - USA
 860 Ridge Lake Blvd.
 Memphis, TN 38120
www.tnb.com

T&B Technical Support
 MS 3B-50
 860 Ridge Lake Blvd.
 Memphis, TN 38120

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com