



Actual

**Catalog Number:** C112-BC2  
**Product ID:** 7TCA298010R0296  
**EAN Number:** 05020963024245  
**Status:** Active

Hinged Connector Interface Fitting, Straight, 2-Way Bosch Compact Connector to Conduit, Conduit Size NC12/NW10, Operating Temperature -40 to 120 Degrees Celsius, RoHS Compliant, IP40 Rating, Very High UV Protection, Polyamide (Nylon), Black

### North American Specifications (UNSPSC)

|                          |                                                            |
|--------------------------|------------------------------------------------------------|
| UNSPSC                   | 39121421 Electrical connector assembly                     |
| IGCC                     | 4586 Electrical connector assembly                         |
| Brand Name               | Harnessflex                                                |
| Type                     | Hinged Bosch Compact Connector to Conduit                  |
| Special Features         | High Pull-Off Strength                                     |
| Application              | Provide Connection Between Connector Interface and Conduit |
| Standard                 | RoHS Compliant                                             |
| Size                     | Conduit Size NC12/NW10                                     |
| Connection               | Straight, 2-Way Connection                                 |
| Material                 | Polyamide/Nylon                                            |
| Color                    | Black                                                      |
| Insulation               | IP40                                                       |
| Temperature Rating       | -40 to 120 Degrees C                                       |
| Environmental Conditions | Very High UV Protection                                    |

### Packaging

|                           |                   |
|---------------------------|-------------------|
| Outer Quantity            | 500               |
| Outer Dimensions (inches) | 15.1x13.1x7.3     |
| Weight Uom                | 0.42 lbs. per 100 |

### Header

|          |                      |
|----------|----------------------|
| 3D Model | Available on Website |
|----------|----------------------|

### For further technical assistance, please contact us...

Thomas & Betts - USA  
 860 Ridge Lake Blvd.  
 Memphis, TN 38120  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
 MS 3B-50  
 860 Ridge Lake Blvd.  
 Memphis, TN 38120

Hours: 7AM - 6PM CDT  
 Monday-Friday  
 Phone: (888) 862-3289  
 Fax: (901) 252-1321  
 Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)