

**Catalog Number:** CPO500-5-B  
**Product ID:** 7TAA017980R0070  
**UPC Number:** 78621083524  
**Status:** A



Thin-Wall Heat Shrinkable Tubing, Green Cross-Linked Polyolefin, 1/2 Inch, Shrink Ratio 2:1, Operating Temperature -55 to 135 Degrees Celsius, Non-Lined, Bulk

- Flame-retardant, cross-linked polyolefin.
- Meets UL 224, 125°C; CSA 22.2 No. 198.1, 125°C; MIL-DTL-23053/5 Class 1&2; AMS 3636 & 3637; DEF STAN 59-97, Issue 3, Type 2a

Actual

### North American Specifications (UNSPSC)

|                  |   |
|------------------|---|
| UNSPSC           | 39121723 Heat shrinkable tube             |
| IGCC             | 5073 Heat shrinkable tube                 |
| Type             | Thin-Wall Heat Shrinkable Tubing          |
| Special Features | Flame-retardant, cross-linked polyolefin. |
| Shrink Ratio     | 2:1                                       |
| Thickness        | Thin                                      |
| Length           | 400 ft                                    |
| Color            | Green                                     |

### European Specifications (ETIM)

|                                   |                        |
|-----------------------------------|------------------------|
| ETIM                              | EC000217 Shrink tubing |
| Type                              | Heat-shrink            |
| Model                             | Thin-walled            |
| Shrink rate                       | 2:1                    |
| Inner diameter before heat-shrink | 12.7mm                 |
| Inner diameter after heat-shrink  | 6.35mm                 |
| Nominal diameter inch             | 1/2 inch               |
| Wall thickness after shrinking    | 1.22mm                 |
| Length                            | 122m                   |
| Operation temperature             | -55-+135°C             |
| Colour                            | Green                  |
| Material                          | Polyolefin (PO-X)      |
| Halogen free                      | N                      |
| With inner glue                   | N                      |
| Printable                         | N                      |
| UL approval                       | Y                      |

### Packaging

|                           |               |
|---------------------------|---------------|
| Outer Quantity            | 1             |
| Outer Dimensions (inches) | 20.3x21.2x5   |
| Weight Uom                | 7.2 lbs. Each |

### Documents / Support Tools

|                                   |                      |
|-----------------------------------|----------------------|
| Technical Drawing / Data Sheet US | Available on Website |
| Catalog Page                      | Available on Website |
| Safety Data Sheet (SDS) Global    | SDS-00046-TB2        |