

**Catalog Number:** DIGB 50  
**Product ID:** 7TAA117120R0007  
**UPC Number:** 02338652805  
**Status:** Active

1/2 Inch, Insulated Grounding Bushing, Die Cast Zinc, 105 Degree C, Thermoplastic Liner

**North American Specifications (UNSPSC)**

|             |                                 |
|-------------|---------------------------------|
| UNSPSC      | 39121312 Electrical bushing     |
| IGCC        | 4442 Electrical bushing         |
| Brand Name  | Steel City                      |
| Type        | Insulated Ground Bushing        |
| Application | For Use with Rigid/IMC Conduits |
| Size        | 1/2 Inch                        |
| Material    | Zinc Die Cast                   |

**European Specifications (ETIM)**

|                             |                            |
|-----------------------------|----------------------------|
| ETIM                        | EC002357 Support insulator |
| Bolt dimension metric (M..) | 12.7                       |

**Packaging**

|                           |                   |
|---------------------------|-------------------|
| Inner Quantity            | 25                |
| Outer Quantity            | 250               |
| Outer Dimensions (inches) | 10.67x7.37x19.25  |
| Weight Uom                | 6.25 lbs. per 100 |

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
www.tnb.com

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email:techsupport@tnb.com