



Actual

**Catalog Number:** EX-M20  
**Product ID:** 7TCA297140R0013  
**UPC Number:** 78621019118  
**EAN Number:** 05011949014657  
**Status:** A

Stopping Plug, M20 Thread, Suitable for Use in Zones 1, 2 , 21, and 22, Exe I, Exe II, and Extd IIIC, IP66-68 Rating, Flame Retardant Polyamide (Nylon 6), Black

**North American Specifications (UNSPSC)**

UNSPSC	39121404 Electrical sleeves
IGCC	4529 Cable end sleeve
Type	Conduit Stopping Plug
Application	Provide Protection for the End of Conduit Systems
Standard	ATEX :- Baseefa 08ATEX0324, IECEx :- IECEx BAS08.0109
Insulation	IP66-68
Material	Flame Retardant Polyamide/Nylon 6
Color	Black
Size	M20 Thread

**European Specifications (ETIM)**

ETIM	EC000032 Plug for cable screw gland
Thread type	Metric
Nominal thread size metric/PG	20
Material	Plastic
Material quality	Polyamide (PA)
Surface protection	Untreated
Colour	Black
For Ex-zone gas	1, 2
For Ex-Zone dust	21, 22

**Packaging**

Inner Quantity	10
Inner Dimensions (inches)	1x1x1
Outer Quantity	2000
Outer Dimensions (inches)	1x1x1
Weight Uom	0.01 lbs. Each