

**Catalog Number:** EXSB0410  
**Product ID:** 7TCA297120R0250  
**EAN Number:** 05011949002050  
**Status:** Active



Actual

Liquid Tight Metallic Conduit, Oil and Dilute Acid Resistant, Conduit Size 20mm, Minimum Bore 16mm, Reel Length 10 Meters, 316 Stainless Steel Core with Flame Retardant PVC Covering, Black

### North American Specifications (UNSPSC)

UNSPSC	39131706 Electrical conduit
IGCC	5543 Liquid Tight Conduit
Brand Name	Kopex
Type	Liquid Tight Metallic Conduit
Special Features	Flame Retardant PVC Covering
Application	Connection for Conduit Systems when Oil and Acid Resistance is Needed
Standard	IEC 61386
Trade Size	20mm
Inside Diameter	16mm
Length	10 Meters
Material	316 Stainless Steel Core with Flame Retardant PVC Covering
Color	Black

### European Specifications (ETIM)

ETIM	EC001179 Protective metallic hose
Nominal diameter	20mm
Nominal size in inch	1/2 inch
Inner diameter	16mm
Material	Stainless steel
Surface protection	Untreated
Sheathing material 1st coating	PVC, flame retardant
Operating temperature	-20-+70°C
Colour	Black
Bending strength	Flexible
Approved according to DIN EN 61386-23 Y	

### Packaging

Outer Quantity	1
Outer Dimensions (inches)	1x1x1
Weight Uom	8.11 lbs. Each

### Header

3D Model	Available on Website
----------	----------------------

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
 860 Ridge Lake Blvd.  
 Memphis, TN 38120  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
 MS 3B-50  
 860 Ridge Lake Blvd.  
 Memphis, TN 38120

Hours: 7AM - 6PM CDT  
 Monday-Friday  
 Phone: (888) 862-3289  
 Fax: (901) 252-1321  
 Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)