

Catalog Number: EXST0530
Product ID: 7TCA297120R0309
EAN Number: 05011949002425
Status: Active



Actual

Liquid Tight Metallic Conduit, Low Fire Hazard, Conduit Size 25mm, Minimum Bore 21mm, Reel Length 30 Meters, Stainless Steel Core with LFH Coating, Black

North American Specifications (UNSPSC)

UNSPSC	39131706 Electrical conduit
IGCC	5543 Liquid Tight Conduit
Brand Name	Kopex
Type	Liquid Tight Metallic Conduit
Special Features	Limited Fire Hazard, Zero Halogen (BS6425 Pt1)
Application	Connection for Conduit Systems when Low Fire Hazard is Needed
Standard	LUL compliant (E1042A6)
Trade Size	25mm
Inside Diameter	21mm
Length	30 Meters
Material	Stainless Steel Core and Low Fire Hazard Coating
Color	Black

European Specifications (ETIM)

ETIM	EC001179 Protective metallic hose
Nominal diameter	25mm
Nominal size in inch	3/4 inch
Inner diameter	21mm
Material	Steel
Surface protection	Other
Sheathing material 1st coating	Megolon, flame retardant
Operating temperature	-20-+70°C
Colour	Black
Bending strength	Flexible
Approved according to DIN EN 61386-23 Y	

Packaging

Outer Quantity	1
Outer Dimensions (inches)	1x1x1
Weight Uom	32.26 lbs. Each

Header

3D Model	Available on Website
----------	----------------------

For further technical assistance, please contact us...

Thomas & Betts - USA
 860 Ridge Lake Blvd.
 Memphis, TN 38120
www.tnb.com

T&B Technical Support
 MS 3B-50
 860 Ridge Lake Blvd.
 Memphis, TN 38120

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com