



Family

Catalog Number: F.66.08SW
Product ID: 7TAA292910R0029
UPC Number: 78620995647
EAN Number: 07630030238987
Status: Active

Black Braided Hose, (F66) Material - Polyamide 6,6, Conduit Size NW - 08

- High temperature stability
- Self extinguishing UL 94 V2
- Free from halogens
- Rail
- Industry, aviation, construction of vehicles and trains
- For bundling and protection of electrical wires and cables

North American Specifications (UNSPSC)

UNSPSC	39131706 Electrical conduit
IGCC	5535 Electrical conduit
Brand Name	PMA
Type	Braided Hose
Application	Machine
Trade Size	NW08
Length	100 m
Flexibility	Medium Flexibility
Material	Polyamide/Nylon 6.6
Color	Black

European Specifications (ETIM)

ETIM	EC001182 Braided hose
Nominal diameter	8mm
Bundle diameter	7-10mm
Material	Plastic
Material quality	Polyamide (PA)
Halogen free	Y
Surface protection	Untreated
Colour	Black
Open (mountable afterwards)	N
Temperature	-55 - +125°C
Fire resistance in accordance with UL94	V2
Approved according to UR	Y
Approved according to DIN 5510	Y
Approved according to NF F 16-101	Y

Packaging

Inner Quantity	1
Outer Quantity	4
Outer Dimensions (inches)	15.748x11.811x7.874
Weight Uom	0.01 lbs. Each

For further technical assistance, please contact us...

Thomas & Betts - USA
 860 Ridge Lake Blvd.
 Memphis, TN 38120
www.tnb.com

T&B Technical Support
 MS 3B-50
 860 Ridge Lake Blvd.
 Memphis, TN 38120

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com