



Actual

Catalog Number: FFPT6-BLK
Product ID: 7TAA003810R0005
UPC Number: 78599107460
Status: A

Furniture Feed Poke-Through, Junction Box Volume 27 Cubic Inches, Cover Diameter 8 Inches, Depth 19-1/4 Inches, Threaded Hubs 3/4 Inch, 1-1/4 Inch, or 2 Inch, Knockout Size 1/2 Inch and 3/4 Inch, Core Drill Size 6 Inches, Finish Black Powder Coated Aluminum

- Power and/or communications connections: 3/4 Inch, 1-1/4 Inch, or 2 Inch threaded hubs
- Core drill size: 6 Inches
- Solid brass, black and brushed aluminum cover finish provide superior aesthetics and durability
- Integral junction box features (5) 1/2 Inch and (5) 3/4 Inch knockouts(27 cubic inch capacity)
- UL 263 - 2-hour fire test
- Custom pre-wired floor box assemblies now available through our eFab department

North American Specifications (UNSPSC)

UNSPSC	39121328 Fire rated poke through box
IGCC	4482 Fire rated poke through box
Brand Name	Steel City
Special Features	Power and/or communications connections: 3/4 Inch, 1-1/4 Inch or 2 Inch threaded hubs
Material	Steel
Cable Entry	Knockouts
Color	Black
Cubic Capacity	27 cu in
Knockouts	10

European Specifications (ETIM)

ETIM	EC000024 Installation box for underfloor-installation
Cover model	Round
Suitable for sub-floor duct	Y
Suitable for hollow floor	Y
With opening carpeting	Y
Colour	Black

Packaging

Outer Quantity	1
Outer Dimensions (inches)	17.87x10.12x8.18
Weight Uom	8.81 lbs. Each

Documents / Support Tools

Technical Drawing / Data Sheet	WSD-001518
Instruction Sheet	TA04738-TB2