



Actual

**Catalog Number:** FFPT6-BRS  
**Product ID:** 7TAA003810R0003  
**UPC Number:** 78599107456  
**Status:** A

Furniture Feed Poke-Through, Junction Box Volume 27 Cubic Inches, Cover Diameter 8 Inches, Depth 19-1/4 Inches, Threaded Hubs 3/4 Inch, 1-1/4 Inch, or 2 Inch, Knockout Size 1/2 Inch and 3/4 Inch, Core Drill Size 6 Inches, Finish Brass

- Power and/or communications connections: 3/4 Inch, 1-1/4 Inch, or 2 Inch threaded hubs
- Core drill size: 6 Inches
- Solid brass, black and brushed aluminum cover finish provide superior aesthetics and durability
- Integral junction box features (5) 1/2 Inch and (5) 3/4 Inch knockouts(27 cubic inch capacity)
- UL 263 - 2-hour fire test
- Custom pre-wired floor box assemblies now available through our eFab department

**North American Specifications (UNSPSC)**

UNSPSC	39121328 Fire rated poke through box
IGCC	4482 Fire rated poke through box
Special Features	Power and/or communications connections: 3/4 Inch, 1-1/4 Inch or 2 Inch threaded hubs
Material	Steel
Cable Entry	Knockouts
Color	Brass
Cubic Capacity	27 cu in
Knockouts	10

**European Specifications (ETIM)**

ETIM	EC000024 Installation box for underfloor-installation
Cover model	Round
Suitable for sub-floor duct	Y
Suitable for hollow floor	Y
With opening carpeting	Y
Colour	Other

**Packaging**

Outer Quantity	1
Outer Dimensions (inches)	17.87x10.12x8.18
Weight Uom	10.71 lbs. Each

**Documents / Support Tools**

Technical Drawing / Data Sheet	WSD-001518
Instruction Sheet	TA04738-TB2