



Representative

Catalog Number: H125CAP
Product ID: 7TBD013430R0009
UPC Number: 78621004479
Status: A

1-1/4 Inch Zinc Capoff with Thermoplastic Insulating Throat, Sealing Ring Nitrile (BUNA-N) for Use with Rigid/IMC Conduit

- CSA Certified for hazardous locations Class II Groups E.F.G. Class III
- Meets NEMA sealing requirements for NEMA 3R, 4 & 13 enclosures.

North American Specifications (UNSPSC)

UNSPSC	39131707 Electrical conduit coupling
IGCC	5548 Electrical conduit coupling
Type	Hubs & Accessories
Special Features	Insulating Throat with a Thermoplastic Temperature Rating of 105 Degrees Celsius
Application	For Use with Rigid/IMC Conduit
Standard	UL E23018, CSA
Trade Size	1-1/4 in
Outside Diameter	2-3/8 in
Length	1-25/32 in
Material	Zinc

European Specifications (ETIM)

ETIM	EC001180 Screw connection for protective metallic hose
Nominal size in inch	1 1/4 inch
Model	Straight
Revolving thread	N
Connection type screw connection to housing	Thread
Thread type	NPT
Material housing	Zinc die-cast
Approved in combination with protective conduit CSA	Y
Approved in combination with protective conduit UL	Y
Operating temperature	0-+105°C

Packaging

Inner Quantity	5
Outer Quantity	50
Outer Dimensions (inches)	21.9x8.88x4.19
Weight Uom	48 lbs. per 100

Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
-----------------------------------	----------------------

Header

3D Model	Available on Website
----------	----------------------