



Actual

**Catalog Number:** HSB520-135-4  
**Product ID:** 7TAA017980R0098  
**UPC Number:** 78621027607  
**Status:** A

Heat-Shrinkable HSB Series Breakout Boots for Cable Range 4/0 - 1000 MCM, Expanded Dia. 5.25, Length 10.02 inch, rated for 600 Volt, 90 degrees continuous use, Material: Cross-linked polyolefin with thermoplastic adhesive liner, Black

- Boots for 2-, 3- and 4-way cable breakouts.
- Thermoplastic Adhesive Liner for complete environment protection and insulation.
- Strain relief and mechanical protection.

#### North American Specifications (UNSPSC)

UNSPSC	39121723 Heat shrinkable tube
IGCC	5073 Heat shrinkable tube
Type	Heavy-Wall Heat Shrinkable Tubing
Special Features	Boots for 2-, 3- and 4-way cable breakouts.
Shrink Ratio	3:1
Thickness	0.13 in ; 3.3 mm
Length	10.02 in ; 254.51 mm
Color	Black

#### European Specifications (ETIM)

ETIM	EC002464 Spreader cap
Type	Heat-shrink
Model	For 4-core cables
Diameter shaft before shrink	133.4mm
Diameter shaft after shrink	34.3mm
Total length after shrink	254.4mm
Inner diameter finger before shrink	76.2mm
Inner diameter finger after shrink	14mm
Operation temperature	-55-+135°C

#### Packaging

Inner Quantity	1
Inner Dimensions (inches)	5.3x5.3x1.5
Outer Quantity	5
Outer Dimensions (inches)	16x6.75x16
Weight Uom	5.25 lbs. Each

#### Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
Instruction Sheet	TA00471-TB2