

Catalog Number: HSMW400-3.00
Product ID: 7TAA017210R0008
UPC Number: 78621083366
Status: Active



Actual

Heat Shrink Tubing, Medium Wall, Shrink Ratio 3:1, Adhesive Lined, .400 Inch Diameter, Black, Rated 600 Volt, 125 Degree C, 3 Inch Lengths

North American Specifications (UNSPSC)

UNSPSC	39121723 Heat shrinkable tube
IGCC	5073 Heat shrinkable tube
Brand Name	Shrink-Kon
Type	Heat Shrink Tubing
Shrink Ratio	3:1
Voltage Rating	600V
Length	3 in ; 76.2 mm
Dielectric Strength	500 V/Mil (20kV/mm)
Volume Resistivity	1016 ohm-cm
Continuous Operating Temperature	-67 Degrees F (-55 C) to 230 Degrees F (110 C)
Minimum Shrink Temperature	248 Degrees F (120 C)
Water Absorption	0.10%
Color	Black

European Specifications (ETIM)

ETIM	EC000217 Shrink tubing
Type	Heat-shrink
Model	Medium-walled
Shrink rate	3:1
Inner diameter before heat-shrink	10.16mm
Inner diameter after heat-shrink	3.81mm
Nominal diameter inch	Other
Wall thickness after shrinking	2.032mm
Length	0.0762m
Operation temperature	-55-+110°C
Colour	Black
Material	Polyolefin (PO-X)
Halogen free	N
With inner glue	Y
Printable	N
UL approval	N

Packaging

Outer Quantity	1200
Outer Dimensions (inches)	4x51x4
Weight Uom	20.31 lbs. per 100

Documents / Support Tools

Safety Data Sheet (SDS) Global	SDS-00046-TB2
--------------------------------	---------------