



Actual

**Catalog Number:** JE10  
**Product ID:** 7TAA057050R0164  
**UPC Number:** 70891715324  
**Status:** Active

J-Line 100 Amp, 20 degreeAngle Enclosure, Painted, 2 inch Standard Conduit Size

### North American Specifications (UNSPSC)

UNSPSC	39121324 Electrical general purpose enclosure
IGCC	4476 Electrical general purpose enclosure
Brand Name	Russellstoll
Type	J-Line Interconnection Systems
Special Features	One-piece interior assemblies interchangeable from regular to reverse service in the field with a screw-driver. Reversed contacts flexibility within any housing.
Application	Value alternative to MaxGard« in 3 Pole 4 Wire, 30 to 200 Amp applications with less severe need.

### Packaging

Inner Quantity	1
Inner Dimensions (inches)	7.13x7.13x6
Outer Quantity	4
Weight Uom	2.8 lbs. Each

### Documents / Support Tools

Technical Data Sheet CA	Available on Website
-------------------------	----------------------

For further technical assistance, please contact us...

Thomas & Betts - USA  
 8155 T&B Blvd.  
 Memphis, TN 38125  
 www.tnb.com

T&B Technical Support  
 MS 3B-50  
 8155 T&B Blvd.  
 Memphis, TN 38125

Hours: 7AM - 6PM CDT  
 Monday-Friday  
 Phone: (888) 862-3289  
 Fax: (901) 252-1321  
 Email:techsupport@tnb.com