



Actual

Catalog Number: LNB/M25
Product ID: 7TCA296050R0299
EAN Number: 05020963002144
Status: Active

Nickel Plated Brass Locknut, Metric Thread Size M25

North American Specifications (UNSPSC)

UNSPSC	31161716 Locknuts
IGCC	2849 Locknuts
Brand Name	Adaptaflex
Type	Locknut with Metric Threads
Application	To Be Used with Fittings When Securing Into Knockouts
Material of Construction	Nickel Plated Brass
Thread Size	M25
Thread Type	Metric
Color	Metallic

European Specifications (ETIM)

ETIM	EC000940 Locknut for cable screw gland
Thread type	Metric
Nominal thread size metric/PG	25
Pitch thread	1.5mm
Material	Metal
Material quality	Brass
Surface protection	Nickel-plated
Colour	Natural colour

Packaging

Inner Quantity	10
Outer Quantity	1000
Outer Dimensions (inches)	14x14x6
Weight Uom	1.87 lbs. per 100

Header

3D Model	Available on Website
----------	----------------------

For further technical assistance, please contact us...

Thomas & Betts - USA
 860 Ridge Lake Blvd.
 Memphis, TN 38120
www.tnb.com

T&B Technical Support
 MS 3B-50
 860 Ridge Lake Blvd.
 Memphis, TN 38120

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com