



Catalog Number: LTC050GY-1000
Product ID: 7TAD012620R0005
UPC Number: 78599121083
Status: A



Actual

Commercial Grade, Type B Liquidtight Flexible PVC Conduit, 1/2 Inch Conduit Size, Approved for Outdoor and Direct Burial in the US, UL Temperature Ratings - 80 Degrees C Dry, 60 Degree C Wet, 70 Degree C Oil, Oil Resistant, Voltage Rating 600V, Gray, 1,000 Foot Reel

- Fast installation, even in tight or cramped spaces.
- Smooth inner diameter allows easy wire pulling.
- Smooth outer jacket uses material approved for outdoor use, is sunlight resistant and oil resistant.
- Lightweight and liquidtight.
- UL Listed for direct burial

North American Specifications (UNSPSC)

UNSPSC	39131706 Electrical conduit
IGCC	5535 Electrical conduit
Type	Liquidtight Flexible Non-Metallic Conduit
Special Features	The Smooth Inner Surface Ensures that Cables and Conductors Can Be Fed Through Very Easily
Application	Machine Tools, Motor Hookups, Food Processing Equipment, Extensions from Wire Ways, and Sensor and Micro Switch Wiring Found In Control Consoles.
Standard	UL E95745, CSA
Trade Size	1/2 in
Outside Diameter	21.3 mm
Inside Diameter	15.8 mm
Length	1,000 ft
Voltage Rating	600 V
Material	PVC
Color	Gray

European Specifications (ETIM)

ETIM	EC001177 Protective plastic hose
Nominal size in inch	1/2 inch
Material	PVC
Operating temperature	-18-+105°C
Flexibility	Flexible
Colour	Grey
Approved according to CSA	Y

Packaging

Outer Quantity	1000
Outer Dimensions (inches)	18x10x30
Weight Uom	13.5 lbs. per 100

Documents / Support Tools

Technical Drawing / Data Sheet	TDS000138
--------------------------------	-----------

