

**Catalog Number:** LTFES03W-C  
**Product ID:** 7TAA012LQ0R0002  
**UPC Number:** 78621011608  
**EAN Number:** 05415022446180  
**Status:** Active



Liquid Tight Flexible Metallic Conduit, Food and Beverage Grade, Galvanized Steel Core with PVC Jacket, Conduit Size 3/4 Inch, Length 30 Meters/100 Feet, Working Temperature -20 to 80 Degrees C, Compliant to RoHS and WEEE, White

Actual

### North American Specifications (UNSPSC)

UNSPSC	39131706 Electrical conduit
IGCC	5543 Liquid Tight Conduit
Brand Name	T&B
Type	Flexible Metal Conduit
Standard	RoHS, WEEE
Trade Size	3/4 Inch
Outside Diameter	1.05
Inside Diameter	0.82
Length	100 ft
Material	Galvanized Steel Core with PVC Jacket
Color	White

### European Specifications (ETIM)

ETIM	EC001179 Protective metallic hose
Nominal diameter	25mm
Nominal size in inch	3/4 inch
Material	Steel
Surface protection	Other
Sheathing material 2nd coating (exterior)	PVC
Operating temperature	-20-+80°C
Colour	White
Bending strength	Flexible

### Packaging

Outer Quantity	100
Outer Dimensions (inches)	20.75x20.38x8
Weight Uom	0.33 lbs. Each

### Documents / Support Tools

Technical Drawing / Data Sheet	TDS000022
Technical Drawing / Data Sheet	TDS000117
Technical Drawing / Data Sheet Canada	TDS000022
Catalog US	Available on Website