

Catalog Number: **MPNK-M207**
Product ID: 7TCA292000R4719
UPC Number: 78621016913
EAN Number: 07630030293412
Status: Active

Conduit Fitting for High Temperature Applications, Fine Profile, Conduit Size NW17, Thread Size M20x1.5, Nickel-Plated Brass with Silicon Seals, IP68, Temperature Range -60 to +260 Degrees Celsius

Packaging

Inner Quantity	10
Inner Dimensions (inches)	11.52x7.8x3.94
Outer Quantity	50
Outer Dimensions (inches)	11.81x7.87x8.66
Weight Uom	0.16 lbs. Each

For further technical assistance, please contact us...

Thomas & Betts - USA
860 Ridge Lake Blvd.
Memphis, TN 38120
www.tnb.com

T&B Technical Support
MS 3B-50
860 Ridge Lake Blvd.
Memphis, TN 38120

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com