



Actual

Catalog Number: TCZ347
Product ID: 7TAG009820R0055
UPC Number: 78621089049
EAN Number: 05414363059462
Status: A

Four-Way and Two-Way Mounting Base With Open Leg Design, Green ETFE for Temperatures up to 170 Degrees Celsius (338 F), Length of 28.6mm (1.13 Inches), Width of 28.6mm (1.13 Inches), Height of 8.5mm (0.33 Inches), Screw Mounting Method, #8 Screw, Mounting Hole Size of 4.4mm (0.17 Inches), Bulk Pack

- Accommodates 4-way for ties up to .091 and 2-way for ties up to .301 maximum width.

North American Specifications (UNSPSC)

UNSPSC	39121717 Cable tie mounts
IGCC	5065 Cable tie mounts
Type	Mounting Base
Special Features	Accommodates 4-way for ties up to .091 and 2-way for ties up to .301 maximum width.
Material	Fluoropolymer
Color	Green
Mounting	Screw
Operating Temperature	-50 to +388 F

European Specifications (ETIM)

ETIM	EC000449 Mounting base and -element for cable ties
Length	28.58mm
Width	28.58mm
Height	8.53mm
Suitable for cable tie width to	7.6mm
Type of fastening	Other
Diameter mounting hole	4.4mm
Material	Plastic
Material quality	Other
Operating temperature	-50-+338°C
Colour	Green

Packaging

Inner Quantity	500
Outer Quantity	5000
Outer Dimensions (inches)	21x13.4x9.5
Weight Uom	5.63 lbs. per 1000

Documents / Support Tools

Technical Drawing / Data Sheet	WSD-000166
--------------------------------	------------