



Actual

Catalog Number: 035-72775-1
Product ID: 7TBD012360R0000
UPC Number: 78621086858
Status: A

1/2 Inch Straight Die Cast Zinc Liquidtight Strain Relief Cord Connector, Cord Range 0.125 to 0.250

- Extended range with superior strain relief

North American Specifications (UNSPSC)

UNSPSC	39121420 Liquid tight connectors
IGCC	4585 Liquid tight connectors
Type	Strain Relief Cord Connectors-Straight
Special Features	Throat Inner Diameter is Nylon Coated for Ease of Wire Pull
Application	Provide Means for Passing a Cord Cable, Armored or Unarmored, Into an Enclosure, Through a Bulk-head or Into a Rigid Conduit
Size	1/2 Inch
Material	Zinc Die Cast

European Specifications (ETIM)

ETIM	EC001180 Screw connection for protective metallic hose
Nominal size in inch	1/2 inch
Model	Straight
Revolving thread	N
Construction type	External thread
Connection type screw connection to housing	Thread
Thread type	NPT
Thread connection size	None
Material housing	Zinc die-cast

Packaging

Inner Quantity	25
Inner Dimensions (inches)	5.3x4.6x3.4
Outer Quantity	100
Outer Dimensions (inches)	10.9x9.9x4.2
Weight Uom	15 lbs. per 100