



Representative

Catalog Number: NCG-PG112G
Product ID: 7TCA303070R0215
UPC Number: 78621015364
EAN Number: 05415022425482
Status: A

Non Armoured Cable Gland, Thread Size PG11, Cable Range 5 to 10 Millimeters, Thread Length 8 Millimeters, Nylon, Grey

- Low profile compact cable glands
- Wide cable clamping range
- Good corrosion resistance

North American Specifications (UNSPSC)

UNSPSC	39121431 Cable gland connector
IGCC	4601 Cable gland connector
Brand Name	ABB
Type	Non Armoured Cable Gland
Application	General purpose, Panel building, Light fixture and housings
Standard	UL514B, CSA, RoHS, WEEE, LVD
Size	PG11
Conductor Range	5 to 10 Millimeters
Material	Nylon
Color	Gray
NEMA Rating	4
Temperature Rating	-20 to +100 Degrees C

European Specifications (ETIM)

ETIM	EC000441 Cable screw gland
Thread type	PG
Nominal thread size metric/PG	11
Thread length	8mm
Suitable for cable diameter	5 - 10mm
Material	Plastic
Material quality	Polyamide (PA)
Halogen free	Y
Degree of protection (IP)	IP68
Colour	Dark grey
Model	Straight
Operating temperature	-20-+100°C

Packaging

Inner Quantity	10
Inner Dimensions (inches)	7.09x3.54x3.54
Outer Quantity	80
Outer Dimensions (inches)	3.94x15.75x11.02
Weight Uom	0.01 lbs. Each

Documents / Support Tools

Technical Drawing / Data Sheet	TDS000030
Instruction Sheet	TA05283-TB2
Support/Tools	Available on Website

Header

3D Model	Available on Website
----------	----------------------

