

Catalog Number: NCG-PG131B
Product ID: 7TCA303070R0066
UPC Number: 78621015223
EAN Number: 05415022424034
Status: Active

Non Armoured Cable Gland, Thread Size PG13.5, Cable Range 6 to 12 Millimeters, Thread Length 10 Millimeters, Nylon, Black

North American Specifications (UNSPSC)

UNSPSC	39121431 Cable gland connector
IGCC	4601 Cable gland connector
Brand Name	ABB
Type	Non Armoured Cable Gland
Application	General purpose, Panel building, Light fixture and housings
Standard	UL514B, CSA, RoHS, WEEE, LVD
Size	PG13.5
Conductor Range	6 to 12 Millimeters
Material	Nylon
Color	Black
NEMA Rating	NEMA 4
Temperature Rating	-20 to +100 Degrees C

European Specifications (ETIM)

ETIM	EC000441 Cable screw gland
Thread type	PG
Nominal thread size metric/PG	13.5
Thread length	10mm
Suitable for cable diameter	6 - 12mm
Material	Plastic
Material quality	Polyamide (PA)
Halogen free	Y
Degree of protection (IP)	IP68
Colour	Black
Model	Straight
Operating temperature	-20-+100°C

Packaging

Inner Quantity	10
Inner Dimensions (inches)	7.09x3.54x3.54
Outer Quantity	50
Outer Dimensions (inches)	3.94x15.75x11.02
Weight Uom	0.01 lbs. Each