



Actual



Representative



Family

Catalog Number: NPG-0381G
Product ID: 7TCA303070R0020
UPC Number: 78621013850
EAN Number: 05415022403725
Status: A

Quick Connect Cable Gland, Thread Size 3/8 Inch NPT, Cable Range 5 to 10 Millimeters, Thread Length 9 Millimeters, Nylon, Grey

- Single Piece (No locknut required)
- Fast and simple to install
- Low internal profile
- Corrosion resistant

North American Specifications (UNSPSC)

UNSPSC	39121431 Cable gland connector
IGCC	4601 Cable gland connector
Brand Name	ABB
Type	Quick Connect Cable Gland
Application	General purpose, Ideal for Panel building and Volume Installers
Standard	cULus, RoHS, WEEE, LVD
Size	3/8 Inch NPT
Conductor Range	5 to 10 Millimeters
Material	Nylon
Color	Gray
Temperature Rating	-20 to +100 C

European Specifications (ETIM)

ETIM	EC000441 Cable screw gland
Thread type	NPT
Nominal thread size inch/gas pipe thread	3/8 inch
Thread length	9mm
Suitable for cable diameter	5 - 10mm
Material	Plastic
Material quality	Polyamide (PA)
Halogen free	Y
Degree of protection (IP)	IP68
Colour	Dark grey
Model	Straight
Operating temperature	-20-+100°C

Packaging

Inner Quantity	10
Inner Dimensions (inches)	7.09x3.54x3.54
Outer Quantity	40
Outer Dimensions (inches)	3.94x15.75x11.02
Weight Uom	3.2 lbs. per 100

Documents / Support Tools

Technical Drawing / Data Sheet US	TDS000036
Instruction Sheet	TA05285-TB2
Support/Tools	Available on Website



Representative