



Actual



Representative



Family

**Catalog Number:** NPG-0501G  
**Product ID:** 7TCA303070R0021  
**UPC Number:** 78621013851  
**EAN Number:** 05415022403732  
**Status:** A

Quick Connect Cable Gland, Thread Size 1/2 Inch NPT, Cable Range 6 to 12mm, Thread Length 9mm, Nylon, Grey

- Single Piece (No locknut required)
- Fast and simple to install
- Low internal profile
- Corrosion resistant

#### North American Specifications (UNSPSC)

UNSPSC	39121431 Cable gland connector
IGCC	4601 Cable gland connector
Type	Quick Connect Cable Gland
Application	General purpose, Ideal for Panel building and Volume Installers
Standard	cULus, RoHS, WEEE, LVD
Size	1/2 Inch NPT
Conductor Range	6 to 12 Millimeters
Material	Nylon
Color	Gray
Temperature Rating	-20 to +100 C

#### European Specifications (ETIM)

ETIM	EC000441 Cable screw gland
Thread type	NPT
Nominal thread size inch/gas pipe thread	1/2 inch
Thread length	9mm
Suitable for cable diameter	6 - 12mm
Material	Plastic
Material quality	Polyamide (PA)
Halogen free	Y
Degree of protection (IP)	IP68
Colour	Dark grey
Model	Straight
Operating temperature	-20-+100°C

#### Packaging

Inner Quantity	10
Inner Dimensions (inches)	7.09x3.54x3.54
Outer Quantity	40
Outer Dimensions (inches)	3.94x15.75x11.02
Weight Uom	0.01 lbs. Each

#### Documents / Support Tools

Technical Drawing / Data Sheet US	TDS000036
Instruction Sheet	TA05285-TB2
Support/Tools	Available on Website



Representative