



Representative



Representative



Family

Location: Jonesboro

TEC Electric
1900 S Church St

Catalog Number: NPG-0502B
Product ID: 7TCA303070R0017
UPC Number: 78621013847
EAN Number: 05415022403695
Status: A

Quick Connect Cable Gland, Thread Size 1/2 Inch NPT, Cable Range 10 to 14 Millimeters, Thread Length 9 Millimeters, Nylon, Black

- Single Piece (No locknut required)
- Fast and simple to install
- Low internal profile
- Corrosion resistant

North American Specifications (UNSPSC)

| | |
|--------------------|---|
| UNSPSC | 39121431 Cable gland connector |
| IGCC | 4601 Cable gland connector |
| Type | Quick Connect Cable Gland |
| Application | General purpose, Ideal for Panel building and Volume Installers |
| Standard | cULus, RoHS, WEEE, LVD |
| Size | 1/2 Inch NPT |
| Conductor Range | 10 to 14 Millimeters |
| Material | Nylon |
| Color | Black |
| Temperature Rating | -20 to +100 C |

European Specifications (ETIM)

| | |
|--|----------------------------|
| ETIM | EC000441 Cable screw gland |
| Thread type | NPT |
| Nominal thread size inch/gas pipe thread | 1/2 inch |
| Thread length | 9mm |
| Suitable for cable diameter | 10 - 14mm |
| Material | Plastic |
| Material quality | Polyamide (PA) |
| Halogen free | Y |
| Degree of protection (IP) | IP68 |
| Colour | Black |
| Model | Straight |
| Operating temperature | -20-+100°C |

Packaging

| | |
|---------------------------|------------------|
| Inner Quantity | 10 |
| Inner Dimensions (inches) | 7.09x3.54x3.54 |
| Outer Quantity | 30 |
| Outer Dimensions (inches) | 3.94x15.75x11.02 |
| Weight Uom | 0.01 lbs. Each |

Documents / Support Tools

| | |
|-----------------------------------|-----------|
| Technical Drawing / Data Sheet US | TDS000036 |
|-----------------------------------|-----------|

Instruction Sheet
Support/Tools

TA05285-TB2
Available on Website



Representative