



Actual



Representative



Family

**Catalog Number:** NPG-0502G  
**Product ID:** 7TCA303070R0022  
**UPC Number:** 78621013852  
**EAN Number:** 05415022403749  
**Status:** Active

Quick Connect Cable Gland, Thread Size 1/2 Inch NPT, Cable Range 7 to 13 Millimeters, Thread Length 9 Millimeters, Nylon, Grey

- Single Piece (No locknut required)
- Fast and simple to install
- Low internal profile
- Corrosion resistant

### North American Specifications (UNSPSC)

UNSPSC	39121431 Cable gland connector
IGCC	4601 Cable gland connector
Brand Name	T&B
Type	Quick Connect Cable Gland
Application	General purpose, Ideal for Panel building and Volume Installers
Standard	cULus, RoHS, WEEE, LVD
Size	1/2 Inch NPT
Conductor Range	7 to 13 Millimeters
Material	Nylon
Color	Gray
Temperature Rating	-20 to +100 Degrees C

### European Specifications (ETIM)

ETIM	EC000441 Cable screw gland
Thread type	NPT
Nominal thread size inch/gas pipe thread	1/2 inch
Thread length	9mm
Suitable for cable diameter	7 - 13mm
Material	Plastic
Material quality	Polyamide (PA)
Halogen free	Y
Degree of protection (IP)	IP68
Colour	Dark grey
Model	Straight
Operating temperature	-20-+100°C

### Packaging

Inner Quantity	10
Inner Dimensions (inches)	7.09x3.54x3.54
Outer Quantity	30
Outer Dimensions (inches)	3.94x15.75x11.02
Weight Uom	4.7 lbs. per 100

### Documents / Support Tools

Technical Drawing / Data Sheet US	TDS000036
Technical Drawing / Data Sheet Canada	TDS000036
Instruction Sheet	TA05285-TB2
Support/Tools	Available on Website



Representative

Thomas & Betts - USA