



Representative



Representative



Family

Catalog Number: NPG-0751B
Product ID: 7TCA303070R0018
UPC Number: 78621013848
EAN Number: 05415022403701
Status: A

Quick Connect Cable Gland, Thread Size 3/4 Inch NPT, Cable Range 13 to 18mm, Thread Length 9mm, Nylon, Black

- Single Piece (No locknut required)
- Fast and simple to install
- Low internal profile
- Corrosion resistant

North American Specifications (UNSPSC)

UNSPSC	39121431 Cable gland connector
IGCC	4601 Cable gland connector
Type	Quick Connect Cable Gland
Application	General purpose, Ideal for Panel building and Volume Installers
Standard	cULus, RoHS, WEEE, LVD
Size	3/4 Inch NPT
Conductor Range	13 to 18 Millimeters
Material	Nylon
Color	Black
Temperature Rating	-20 to +100 C

European Specifications (ETIM)

ETIM	EC000441 Cable screw gland
Thread type	NPT
Nominal thread size inch/gas pipe thread	3/4 inch
Thread length	9mm
Suitable for cable diameter	13 - 18mm
Material	Plastic
Material quality	Polyamide (PA)
Halogen free	Y
Degree of protection (IP)	IP68
Colour	Black
Model	Straight
Operating temperature	-20-+100°C

Packaging

Inner Quantity	10
Inner Dimensions (inches)	7.09x3.54x3.54
Outer Quantity	20
Outer Dimensions (inches)	3.94x15.75x11.02
Weight Uom	0.01 lbs. Each

Documents / Support Tools

Technical Drawing / Data Sheet US	TDS000036
Instruction Sheet	TA05285-TB2
Support/Tools	Available on Website



Representative