



Actual



Representative



Family

Catalog Number: NPG-0751G
Product ID: 7TCA303070R0023
UPC Number: 78621013853
EAN Number: 05415022403756
Status: Active

Quick Connect Cable Gland, Thread Size 3/4 Inch NPT, Cable Range 11 to 17 Millimeters, Thread Length 9 Millimeters, Nylon, Grey

- Single Piece (No locknut required)
- Fast and simple to install
- Low internal profile
- Corrosion resistant

North American Specifications (UNSPSC)

UNSPSC	39121431 Cable gland connector
IGCC	4601 Cable gland connector
Brand Name	T&B
Type	Quick Connect Cable Gland
Application	General purpose, Ideal for Panel building and Volume Installers
Standard	cULus, RoHS, WEEE, LVD
Size	3/4 Inch NPT
Conductor Range	11 to 17 Millimeters
Material	Nylon
Color	Grey
Temperature Rating	-20 to +100 Degrees C

European Specifications (ETIM)

ETIM	EC000441 Cable screw gland
Thread type	NPT
Nominal thread size inch/gas pipe thread	3/4 inch
Thread length	9mm
Suitable for cable diameter	11 - 17mm
Material	Plastic
Material quality	Polyamide (PA)
Halogen free	Y
Degree of protection (IP)	IP68
Colour	Dark grey
Model	Straight
Operating temperature	-20-+100°C

Packaging

Inner Quantity	10
Inner Dimensions (inches)	7.09x3.54x3.54
Outer Quantity	20
Outer Dimensions (inches)	3.94x15.75x11.02
Weight Uom	7 lbs. per 100

Documents / Support Tools

Technical Drawing / Data Sheet US	TDS000036
Technical Drawing / Data Sheet Canada	TDS000036
Instruction Sheet	TA05285-TB2
Support/Tools	Available on Website



Representative

Thomas & Betts - USA