



Actual



Representative



Family

**Catalog Number:** NPG-M251G  
**Product ID:** 7TCA303070R0008  
**UPC Number:** 78621013794  
**EAN Number:** 05415022403329  
**Status:** Active

Quick Connect Cable Gland, Thread Size M25, Cable Range 11 to 17 Millimeters, Thread Length 9 Millimeters, Nylon, Grey

- Single Piece (No locknut required)
- Fast and simple to install
- Low internal profile
- Corrosion resistant

### North American Specifications (UNSPSC)

UNSPSC	39121431 Cable gland connector
IGCC	4601 Cable gland connector
Brand Name	T&B
Type	Quick Connect Cable Gland
Application	General purpose, Ideal for Panel building and Volume Installers
Standard	cULus, RoHS, WEEE, LVD
Size	M25
Conductor Range	11 to 17 Millimeters
Material	Nylon
Color	Gray
Temperature Rating	-20 to +100 Degrees C

### European Specifications (ETIM)

ETIM	EC000441 Cable screw gland
Thread type	Metric
Nominal thread size metric/PG	25
Pitch thread	1.5mm
Thread length	9mm
Suitable for cable diameter	11 - 17mm
Material	Plastic
Material quality	Polyamide (PA)
Halogen free	Y
Degree of protection (IP)	IP68
Colour	Dark grey
Model	Straight
Operating temperature	-20-+100°C

### Packaging

Inner Quantity	10
Inner Dimensions (inches)	7.09x3.54x3.54
Outer Quantity	30
Outer Dimensions (inches)	3.94x15.75x11.02
Weight Uom	0.01 lbs. Each

### Documents / Support Tools

Technical Drawing / Data Sheet US	TDS000036
Technical Drawing / Data Sheet Canada	TDS000036
Instruction Sheet	TA05285-TB2
Support/Tools	Available on Website



Representative

Thomas & Betts - USA