



Actual

**Catalog Number:** PUEG-70B.30  
**Product ID:** 7TAA292360R0044  
**UPC Number:** 78620996874  
**EAN Number:** 07630030264344  
**Status:** A

Highly Flexible, Medium Wall Black Conduit, (PUE) Material - Polyurethane, Conduit Size NW - 70, 30 Meters

- Highest flexibility
- Excellent chafing characteristics
- Free from halogens and cadmium
- For dynamic applications in robotics and automation

**North American Specifications (UNSPSC)**

UNSPSC	39131706 Electrical conduit
IGCC	5535 Electrical conduit
Type	Medium Wall Conduit
Application	Robotic
Trade Size	NW70
Length	30 m
Flexibility	Very High
Material	Polyurethane
Color	Black

**European Specifications (ETIM)**

ETIM	EC001175 Corrugated plastic hose
Nominal diameter	80mm
Outer diameter	80.5mm
Inner diameter	68.2mm
Material	Other
Compressive strength	70N
Operating temperature	-60 - +50°C
Fire resistance in accordance with UL94	HB
UV resistant	Y
Oil resistant	Y
Colour	Black
Sheathing material	Not sheathed
Bending strength	Flexible
Lengthwise slotted	N
Closable (two-part)	N
Halogen free	Y
Approved according to DIN EN 61386-23	N
Approved according to UR	N
Approved according to CSA	N
Approved according to LUL/British Standard	N
Approved according to Lloyd's Register TA	N
Approved according to UTAC	N
Approved according to DIN 5510	N
Approved according to NF F 16-101	N

**Packaging**

Inner Quantity	1
Outer Quantity	2
Outer Dimensions (inches)	45.669x45.669x26.378



Weight Uom

42 lbs. Each