



Actual

Catalog Number: SCG-0503
Product ID: 7TCA303040R0057
UPC Number: 78621015887
EAN Number: 05415022429923
Status: A

Non Armoured Cable Gland, Thread Size 1/2 Inch NPT, Cable Range 10 to 14 Millimeters, Thread Length 13 Millimeters, Stainless Steel

- Low profile compact cable glands
- Wide cable clamping range
- Excellent corrosion resistance
- Ideal for wet locations

North American Specifications (UNSPSC)

UNSPSC	39121431 Cable gland connector
IGCC	4601 Cable gland connector
Brand Name	ABB
Type	Non Armoured Cable Gland
Application	General purpose, Panel building, Light fixture and housings
Standard	cULus, RoHS, WEEE, LVD
Size	1/2 Inch NPT
Conductor Range	10 to 14 Millimeters
Material	316 Stainless Steel
Color	Metallic
NEMA Rating	4
Temperature Rating	-20 to +100 Degrees C

European Specifications (ETIM)

ETIM	EC000441 Cable screw gland
Thread type	NPT
Nominal thread size inch/gas pipe thread	1/2 inch
Thread length	13mm
Suitable for cable diameter	10 - 14mm
Material	Metal
Material quality	Stainless steel V4A
Surface protection	Untreated
Degree of protection (IP)	IP68
Colour	Natural colour
Model	Straight
Operating temperature	-20-+100°C

Packaging

Inner Quantity	10
Inner Dimensions (inches)	7.09x3.54x3.54
Outer Quantity	50
Outer Dimensions (inches)	3.94x15.75x11.02
Weight Uom	0.02 lbs. Each

Documents / Support Tools

Technical Drawing / Data Sheet	TDS000032
Instruction Sheet	TA05283-TB2
Support/Tools	Available on Website

