



Actual

**Catalog Number:** SCG-0752  
**Product ID:** 7TCA303040R0058  
**UPC Number:** 78621015889  
**EAN Number:** 05415022429930  
**Status:** A

Non Armoured Cable Gland, Thread Size 3/4 Inch NPT, Cable Range 13 to 18mm, Thread Length 13mm, Stainless Steel

- Low profile compact cable glands
- Wide cable clamping range
- Excellent corrosion resistance
- Ideal for wet locations

#### North American Specifications (UNSPSC)

UNSPSC	39121431 Cable gland connector
IGCC	4601 Cable gland connector
Type	Non Armoured Cable Gland
Application	General purpose, Panel building, Light fixture and housings
Standard	cULus, RoHS, WEEE, LVD
Size	3/4 Inch NPT
Conductor Range	13 to 18 Millimeters
Material	316 Stainless Steel
Color	Metallic
NEMA Rating	4
Temperature Rating	-20 to +100 C

#### European Specifications (ETIM)

ETIM	EC000441 Cable screw gland
Thread type	NPT
Nominal thread size inch/gas pipe thread	3/4 inch
Thread length	13mm
Suitable for cable diameter	13 - 18mm
Material	Metal
Material quality	Stainless steel V4A
Surface protection	Untreated
Degree of protection (IP)	IP68
Colour	Natural colour
Model	Straight
Operating temperature	-20-+100°C

#### Packaging

Inner Quantity	10
Inner Dimensions (inches)	7.09x3.54x3.54
Outer Quantity	30
Outer Dimensions (inches)	3.94x15.75x11.02
Weight Uom	0.02 lbs. Each

#### Documents / Support Tools

Technical Drawing / Data Sheet	TDS000032
Instruction Sheet	TA05283-TB2
Support/Tools	Available on Website

